

MAC

OIL BATH WITH MAGNETIC STIRRER MSW-279(PRO)

Images for reference purpose only, may change according to model & size

BAKELITE CLAMP

BRACKET

COLUMN STAND

BEAKER HOLDER

STAINLESS STEEL
POT BODY

POWER SWITCH

LED DISPLAY

SETTING KNOB

LED DISPLAY



1000W FAST HEATING

Heat Up to 100°C within 15 minutes



Uniform temperature, more
concentrated heat



Continuous heat output,
precise temperature control,
40% shorter heating time than
traditional agitators

LED

LED Display



Fast Heating



Timing: 0-999h



Speed/Timing
Adjustable



Stainless Steel

PRODUCT DETAILS



High Quality Heat Insulation Board

Effective heat dissipation and thermal insulation protection



External Temperature Sensor

Accurate temperature measurement



Power Switch

One - button operation / power off



304 Stainless Steel Pot Body

Durable and corrosion resistant



LED Display

Using an LED display, simple operation



COLLECTOR HEATING

Rapid heating and uniform temperature, high efficiency

Oil Bath With Magnetic Stirrer Technical Data

Model	#OBMS-0.8(PRO)	#OBMS-3(PRO)	#OBMS-5(PRO)
Display Mode	LED Display	LED Display	LED Display
Maximum Stirring Volume	0.8 Ltrs.	3 Ltrs.	5 Ltrs.
Speed Range	2200 rpm	2800 rpm	2800 rpm
Motor Type	DC Permanent Magnet	DC Permanent Magnet	DC Permanent Magnet
Max Stirring Volume	1 L (H2O)	2 L (H2O)	2 L (H2O)
Temperature Control Range	RT +5°C to 300°C	RT +5°C to 300°C	RT +5°C to 300°C
Temperature Accuracy	±1°C (0 - 100°C)	±1°C (0 - 100°C)	±1°C (0 - 100°C)
Timing Range	0 - 9999min / 0 - 9999hrs	0 - 9999min / 0 - 9999hrs	0 - 9999min / 0 - 9999hrs
Heating Power (W)	500 W	600 W	1000 W
Voltage	AC 220 V	AC 220 V	AC 220 V
Frequency	50 / 60 Hz	50 / 60 Hz	50 / 60 Hz

MAC

B-35/3, G.T. KARNAL ROAD, INDUSTRIAL AREA, DELHI - 110033
 Tel : +91 11 48494849 (100 Lines)
 E-mail : info@macroscientificworks.com
 Web : www.macroscientificworks.com